



- Ø 30mm Dia\_Front
- Ø 22 - 30mm Dia\_Front

**Diameter**

Ø 30mm Dia\_Front Comment

fine

Nominal: 30.0000

ISO286: [ ]

Upper Tol.: 0.1000  None

Lower Tol.: -0.1000  None

Feature 1  
Cylinder\_30mm Dia\_Front

Actual: [ ]

OK Reset

Ø 22 - 30mm Dia\_Front

**Diameter**

Ø 22 - 30mm Dia\_Front Comment

fine

Nominal: 30.0000

ISO286: [ ]


Upper Tol.: 0.1000  None

Lower Tol.: -0.1000  None

Feature 1  
Cylinder\_22 - 30mm Dia\_Front

Actual: [ ]

OK Reset



Run